

PLASTfast / PLAST PERFORMANCE PE 100 SDR 11 (PN16)

Comparison Table

Tavola di confronto - Tabla Comparativa
Tableau comparatif - Tabela Comparativa

Cooling table (example) at 23 °C - Tabella di raffreddamento (esempio) a 23 °C - Tabla de refrigeración (ejemplo) a 23 °C
Table de refroidissement (par exemple) à 23 °C - Tabela arrefecimento (exemplo) a 23 °C

ø	cool time "PLAST" (min)	cool time "PLASTfast" (min)	Performance (%)
50	10	5	+100
63	15	5	+200
75	20	10	+100
90	30	10	+200
110	30	10	+200
125	30	10	+200
140	30	10	+200
160	30	15	+100
180	30	15	+100
200	30	15	+100
225	45	15	+200
250	60	20	+200
280	60	20	+200
315	60	30	+100
355	60	30	+100

Cooling table (example) at 10 °C - Tabella di raffreddamento (esempio) a 10 °C - Tabla de refrigeración (ejemplo) a 10 °C
 Table de refroidissement (par exemple) à 10 °C - Tabela arrefecimento (exemplo) a 10 °C

ø	cool time "PLAST" (min)	cool time "PLASTfast" (min)	Performance (%)
50	10	4	+150
63	15	4	+275
75	20	8	+150
90	30	8	+275
110	30	8	+275
125	30	8	+275
140	30	8	+275
160	30	13	+132
180	30	13	+132
200	30	13	+132
225	45	13	+250
250	60	18	+233
280	60	18	+233
315	60	21	+185
355	60	21	+185

Cooling table (example) at 30 °C - Tabella di raffreddamento (esempio) a 30 °C - Tabla de refrigeración (ejemplo) a 30 °C
 Table de refroidissement (par exemple) à 30 °C - Tabela arrefecimento (exemplo) a 30 °C

ø	cool time "PLAST" (min)	cool time "PLASTfast" (min)	Performance (%)
50	10	7	+50
63	15	7	+100
75	20	14	+40
90	30	14	+100
110	30	14	+100
125	30	14	+100
140	30	14	+100
160	30	21	+40
180	30	21	+40
200	30	21	+40
225	45	21	+110
250	60	30	+100
280	60	30	+100
315	60	42	+42
355	60	42	+42